

# Approved Tubing for use with **ULTRA-FIN**<sup>™</sup> Radiant Floor Heating System

Ultra-Fin is typically designed and installed with 1/2" tubing (5/8" O.D.). Larger diameter PEX tubing may be used up to 3/4" (7/8" O.D.) with larger sized Turnkeys specified.

## **CAUTION!**

**Do Not use tubing with an EVOH barrier on the exterior of the tubing.** However tubing manufactured with a polyethylene layer or non-friction coating extruded over the EVOH oxygen barrier is approved.

Using a tubing brand from our Approved Tubing List will ensure a silent interface between the PEX tubing when attached or crossing wood joist.

### **Recommended Tubing Brands**

<b>PEX Tubing</b>	<b>PEX-AI-PEX Tubing</b>	<b>Pert Tubing</b>
Roth DUOPEX	All Brands	All Brands
Uponor hePEX		
ViegaPEX Barrier		
Rehau RauPEX		
Watts Radiant PEX		
ThermaPEX		
Mr PEX		
Viega FostaPEX (FostaPEX Turnkey required for larger O.D.)		

Other brands of PEX tubing may be acceptable, please check with an Ultra-Fin representative.

Installing other types of tubing may create a slight ticking noise as the tubing expands during operation. This noise is created by the outer layer of the EVOH barrier when it is in direct contact with wood.